

## SHINING 3D SHARES COMPLETE WORKFLOW SOLUTIONS AND MAJOR ANNOUNCEMENTS



■ SHINING 3D focuses entirely on 3D-digitising and 3D-printing solutions, developing a full suite of digital products for both dental clinics and dental laboratories. The SHINING 3D portfolio aims to offer a complete solution covering the needs of both clinics and laboratories, including intra-oral and desktop 3D scanners and digital light processing and liquid crystal display 3D printers.

The exhibition will be a great opportunity to have a closer look and to discover SHINING 3D's complete workflow. Powerful, efficient and user-friendly solutions will be showcased, and attendees will be able to discover news from SHINING 3D exclusively at IDS.

Among the technology on display will be the AccuFab-L4D—a large-platform 3D printer with 4K resolution that supports the printing of different types of professional dental appliances and improves the efficiency of denture fabrication.

SHINING 3D's Aoralscan 3 intra-oral scanner improves the overall clinical experience with its powerful and intelligent data processing capabilities. The scanning speed and the accuracy of the previous model have been improved by up to 30%, allowing for better results.

AutoScan-DS-EX Pro(H) is the latest addition to SHINING 3D's portfolio of desktop scanners. It is equipped with dual 5 MP cameras, achieving a

scanning accuracy of  $\leq 8 \mu\text{m}$  and thus satisfying the requirement of various applications in the dental industry.

This year, SHINING 3D will be making some big announcements, such as the debut of its first wireless intra-oral scanner, Aoralscan 3 Wireless, which provides freedom from constraints and secondary contamination, thus enhancing the whole treatment experience. It includes a fast-heating scanning tip, greatly reduces post-processing time and boasts an outstanding power supply, among its many great features.

MetiSmile is SHINING 3D's first self-developed and manufactured facial scanner for dental applications. It can quickly capture facial information for 3D modelling in vivid texture and features mandibular movement tracking and facial measuring functions.

Fabwash is a multistage part-releasing, washing and drying system built to deliver the ease of use, consistency, speed and cleanliness demanded by dental clinics employing 3D printing. ◀

**SHINING 3D Technology, Germany**  
www.shining3ddental.com  
**Hall 3.1**  
**Booth K040/L049**

## CERAGLOSS HP ZWEISTUFIGES POLIERSYSTEM FÜR KERAMIK PASST SICH JEDER OBERFLÄCHE AN CERAGLOSS HP TWO-STEP POLISHING SYSTEM FOR CERAMICS ADAPTS TO ANY SURFACE STRUCTURE

■ Das zweistufige Lamellenpoliersystem mit Diamantkörnung von Edenta dient der Hochglanzpolitur von Keramikmaterialien. Die einzelnen Lamellen stützen sich während des Poliervorgangs gegenseitig, behalten dabei ihre Flexibilität und passen sich somit jeder Oberflächenstruktur an, um perfekte Polierergergebnisse für die Hochglanzpolitur von okklusalen, labialen, inzisalen, bukkalen und approximalen Bereichen zu erzielen. Die erste Polierstufe (blau) dient der Oberflächen-glättung und Vorbereitung für die Endpolitur. Die zweite Polierstufe (gelb) dient der Hochglanzpolitur ohne zusätzlichen Glanzbrand. Die empfohlene Drehzahl beträgt 5.000 rpm. ◀

■ Edenta's two-step lamella polishing system with diamond grit is used for high-gloss polishing of ceramic materials. The individual lamellae support each other during the polishing process while retaining their flexibility and therefore adapt to every surface structure to create perfect polishing results for high-gloss polishing of occlusal, labial, incisal, buccal and interproximal areas. The



first polishing step (blue) is for surface smoothing and preparation for final polishing. The second polishing step (yellow) is for high-gloss polishing without additional glaze firing. The recommended speed is 5,000 rpm. ◀

**Edenta Etablissement, Liechtenstein**  
www.edenta.com  
**Hall 11.3**  
**Booth A060/B069**

AD

## STOP BY USA PAVILLION HALL 4.2, BOOTH #H41 FOR A FREE SAMPLE!

### HURRICAINE®

Topical Anesthetic  
20% Benzocaine Oral Anesthetic  
ORIGINAL WILD CHERRY FLAVOR



Available in 1 fl. oz. bottles of liquid, 1 oz. bottles of gel and individually wrapped unit dose Snap -n- Go™ Swabs

### 20% Benzocaine for fast, temporary relief of occasional minor irritation and pain associated with:

- Sore mouth and throat
- Canker sores
- Minor dental procedures
- Minor injury of the mouth and gums
- Minor irritation of the mouth and gums caused by dentures or orthodontic appliances

#### EFFECTIVE

- Trusted by dental professionals for over 40 years
- Eliminates pain and discomfort

#### FAST-ACTING

- Relief within 30 seconds

#### SAFE

- Virtually no systemic absorption
- Available over the counter

### HURRIVIEW®



Plaque Indicating Snap -n- Go™ Swabs

### HURRIVIEW II®

Two-Tone Plaque Indicating Snap -n- Go™ Swabs

### HurriView® and HurriView II® highlight where improved oral hygiene is needed

- HurriView highlights plaque in reddish-pink
- HurriView II highlights old plaque in blue and new plaque in reddish-pink
- Helps you show patients where they have plaque build-up & helps motivate them to improve their oral hygiene routines
- Individually wrapped
- In-office evaluation or dispense for home use
- Available in boxes of 72
- No messy rinses or tablets!



### HURRISEAL®

DENTIN DESENSITIZER



#### FAST-ACTING

Chairside results

#### TREATS SENSITIVITY

When used for cervical sensitivity, HurriSeal® will last for 6 to 9 months

#### PREVENTS SENSITIVITY

When applied under restorations, HurriSeal lasts for the lifetime of the restoration

#### EASY TO USE

No mixing or light-curing

#### SOFT TISSUE FRIENDLY

Gentle to soft tissue and does not cause gingival irritation when used as directed

#### INTERESTED IN BECOMING A DISTRIBUTOR?

Beutlich® Pharmaceuticals, LLC is currently looking for distributors worldwide. If interested, please contact Mr. Jason Dominick, International Sales:

TEL: +1-386-225-9322, Email: jdominick@beutlich.com

HurriCaine®, HurriView, HurriView II and HurriSeal are registered trademarks of Beutlich Pharmaceuticals, LLC. Snap -n- Go is a trademark of Beutlich Pharmaceuticals, LLC. www.beutlich.com. IDSAF 713 0123

# Do you want *one impression machine* for your scanning needs?

## NeoScan™ 1000

NeoScan 1000 is a fast, accurate and easy-to-use intraoral scanner that provides the possibility for a flexible workflow, saving you time and money. Best of all, the accuracy is better or equal to top leading brands, with significantly less cost and no license fees. Stop by our booth Hall 11.3 Stand G010-H029 and experience it yourself.



- ✓ Easy to use, fast and accurate
- ✓ Open system for your scanning needs
- ✓ Attractive price and no license fees

