



# VINTAGE PRIME PRESS



High-strength lithium disilicate glass ceramic with new HDIL technology



- High-strength lithium disilicate glass ceramic with biaxial flexural strength of **up to 525 MPa**
- Reliable shade stability even after multiple firing
- High accuracy of fit, as there is almost no reaction layer after pressing
- 4 different translucencies for every restorative challenge
- Combinability with Vintage LD layered porcelains and Vintage Art Universal stains



Hall 11.3  
Stand C010



www.shofu.de

## TODAY LIVE

Fri - March 17

■ 09:30 - 10:30

**Ceramage / Ceramage UP:**  
Aesthetic aspects by using composites with 2 different viscosities for the fabrication of anterior restorations with natural appearance  
Inga Potoczna (DT) / POL

■ 11:00 - 12:00

**BEAUTIFIL composites:**  
Composites simple and easy!  
New approaches to the fabrication of highly aesthetic restorations by using composite in a constructive and efficient way  
Dr Ulf Krueger-Janson (Dentist) / DE

■ 12:30 - 13:30

**Vintage PRO / Vintage Art Universal:**  
Aesthetics of metal-ceramic restorations!  
Vestibular veneering of a central incisor and individual maintaining balance and harmony between hard and soft tissues  
Tomasz Dabrowski (DT) / POL

■ 14:00 - 15:00

**BEAUTIFIL composites:**  
Composites simple and easy!  
New approaches to the fabrication of highly aesthetic restorations by using composite in a constructive and efficient way  
Dr Ulf Krueger-Janson (Dentist) / DE

■ 15:30 - 16:30

**Ceramage / Ceramage UP / Lite Art:**  
Individual anterior tooth design with the best of two composite systems  
Yekaterina Nazarenus (MDT) / KAZ

■ 17:00 - 18:00

**SHOFU Disk ZR Lucent Supra / Vintage Art Universal:**  
Characterisation of posterior zirconia crowns! How to manage the viscosity and chroma of the stains to obtain natural-looking colouring effects  
Marco Zanzottera (DT) / IT