

roots

international magazine of endodontology

3²⁰¹⁰

| clinical report

Crown preparation techniques utilising the operating microscope

| research

Endodontic treatment of primary teeth in the general dental practice

| case report

Removal of a fractured instrument



CALAMUS[®] DUAL

DOWNPACK & BACKFILL

FAST AND TIGHTLY SEALED ROOT CANAL FILLINGS



TIME-SAVING AND LONG-LASTING 3D OBTURATION OF ROOT CANALS

Filling was never so easy!

- Obturation device for downpack and backfill

Device designed for your comfort

- Ergonomically designed handpieces with large operation angle and feather-touch activation by flexible silicone ring

Lateral or vertical obturation? Better results with Calamus[®]

- Vertical condensation is a faster method to achieve a long-lasting, tightly sealed, three dimensional root canal filling
- Reliable obturation of lateral canals as well as minimal risk of root fractures

DENTSPLY
MAILLEFER

www.dentsplymaillefer.com